

Project:

Fixture Type:

Location:

Contact:

P300386-009

Goodwin

Goodwin Collection One-Light Brushed Nickel Modern Vanity Light with Clear Glass

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Width: 4-1/2 in Extends: 5 in Height: 8-3/8 in

H/CTR: 4-3/4 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall vertical	6 inches of wire supplied	(1) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7.25" ht., 1" depth		Fully dimmable with dimmable bulbs	