PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P300386-31M Goodwin

Goodwin Collection One-Light Matte Black Modern Vanity Light with Clear Glass

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 4-1/2 in Extends: 5 in Height: 8-3/8 in H/CTR: 4-3/4 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall vertical	6 inches of wire supplied	(1) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC Lamp Type A19		1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7.25" ht., 1" depth		Fully dimmable with dimmable bulbs	