## **PROGRESS** LIGHTING<sup>™</sup>

Project:	
Fixture Type:	
Location:	

Contact:

## P300387-009 Goodwin

Goodwin Collection Two-Light Brushed Nickel Modern Vanity Light with Clear Glass

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 12-7/8 in Extends: 5 in Height: 8-1/4 in H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(2) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 12.87" W., 4.5" ht., 1" depth	Fully dimmable with dimmable bulbs		