PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P300387-015 Goodwin

Goodwin Collection Two-Light Polished Chrome Modern Vanity Light with Clear Glass

Category: Bath & Vanity Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 12-7/8 in Extends: 5 in Height: 8-1/4 in H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(2) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per socket	
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 12.87" W., 4.5" ht., 1" depth		Fully dimmable with dimmable bulbs	