

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300387-31M
Goodwin

Goodwin Collection Two-Light Matte Black Modern Vanity Light with Clear Glass

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Width: 12-7/8 in
Extends: 5 in
Height: 8-1/4 in
H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical
Width: 3-1/2 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(2) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 12.87" W., 4.5" ht., 1" depth		Fully dimmable with dimmable bulbs	