

Project:		
Fixture Type:		
Location:		
Contact:		



## P300388-015

## Goodwin

Goodwin Collection Three-Light Polished Chrome Modern Vanity Light with Clear Glass

Category: Bath & Vanity
Finish: Polished Chrome (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical

Width: 21 in Extends: 5 in Height: 8-1/4 in

H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

		<u> </u>	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(3) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 21" W., 4.5" ht., 1" depth	Fully dimmable with dimmable bulbs		