

Project:			
Fixture Type:			
Location:			
Contact			



P300389-009

Goodwin

Goodwin Collection Four-Light Brushed Nickel Modern Vanity Light with Clear Glass

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical

Width: 29-1/4 in Extends: 5 in Height: 8-1/4 in

H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

		0 371	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(4) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 29.25" W., 4.5" ht., 1" depth		Fully dimmable with dimmable bulbs	