

Project:		
Fixture Type:		
Location:		
Contact:		



P300389-31M

Goodwin

Goodwin Collection Four-Light Matte Black Modern Vanity Light with Clear Glass

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical

Width: 29-1/4 in Extends: 5 in Height: 8-1/4 in

H/CTR: 5-7/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

	G				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Wall horizontal	6 inches of wire supplied	(4) Medium Base (E26) socket	cULus Damp Location Listed		
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty		
		Incandescent: 60-watt MAX per			
Fixture can be installed with glass		socket			
facing up or down		LED: 12.5-watt MAX per socket			
Canopy covers a standard 4" recessed outlet box: 29.25" W., 4.5" ht., 1" depth	Fully dimmable with dimmable bulbs				