

Project:			
Fixture Type:			
Location:			
Contact			



## P300390-31M

## **Clear Glass**

 $\label{thm:light-matter} \mbox{Two-Light Matte Black Transitional Bath and Vanity Light with Clear Glass for Bathroom}$ 

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Width: 18 in Extends: 8 in Height: 8-3/8 in

H/CTR: 4-7/8 in (glass facing up)

Clear Glass Bell Width: 5-7/8 in Height: 5-1/8 in

			g - ,	
	MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
	Wall horizontal	6 inches of wire supplied	(2) Medium Base (E26) socket	cULus Damp Location Listed
	Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
			Incandescent: 60-watt MAX per	
I	Fixture can be installed with glass		socket	
	facing up or down		LED: 12.5-watt MAX per socket	
	Canopy covers a standard 4" recessed outlet box: 18" W., 4.75" ht., 1" depth		Fully dimmable with dimmable bulbs	