

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |
| Contact: | | |



P300392-009

Clear Glass

Four-Light Brushed Nickel Transitional Bath and Vanity Light with Clear Glass for Bathroom

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Width: 30 in Extends: 8 in Height: 8-3/8 in

H/CTR: 4-7/8 in (glass facing up)

Clear Glass Bell Width: 5-7/8 in Height: 5-1/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------|-------------------------------|----------------------------|
| Wall horizontal | 6 inches of wire supplied | (4) Medium Base (E26) socket | cULus Damp Location Listed |
| Mounting backplate for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| | | Incandescent: 60-watt MAX per | |
| Fixture can be installed with glass | | socket | |
| facing up or down | | LED: 12.5-watt MAX per socket | |
| Canopy covers a standard 4" | | Fully dimmable with dimmable | |
| recessed outlet box: 30" W., 4.75" ht., 1" depth | | bulbs | |