

Project:			
Fixture Type:			
Location:			
Contact:			



## P300392-31M

## **Clear Glass**

Four-Light Matte Black Transitional Bath and Vanity Light with Clear Glass for Bathroom

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Width: 30 in Extends: 8 in Height: 8-3/8 in

H/CTR: 4-7/8 in (glass facing up)

Clear Glass Bell Width: 5-7/8 in Height: 5-1/8 in

		0 , 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(4) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 30" W., 4.75" ht., 1" depth	Fully dimmable with dimmable bulbs		