

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P300393-31M

### Clear Glass

Five-Light Matte Black Transitional Bath and Vanity Light with Clear Glass for Bathroom

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Bell

Width: 36 in  
 Extends: 8 in  
 Height: 8-3/8 in  
 H/CTR: 4-7/8 in (glass facing up)

Clear Glass Bell  
 Width: 5-7/8 in  
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(5) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 36" W., 4.75" ht., 1" depth		Fully dimmable with dimmable bulbs	