

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P300394-31M
Clear Glass

Six-Light Matte Black Transitional Bath and Vanity Light with Clear Glass for Bathroom

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Width: 48 in
 Extends: 8 in
 Height: 8-3/8 in
 H/CTR: 4-7/8 in (glass facing up)

Clear Glass Bell
 Width: 5-7/8 in
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(6) Medium Base (E26) socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 48" W., 4.75" ht., 1" depth		Fully dimmable with dimmable bulbs	