

Project:

Fixture Type:

Location:

Contact:

P300395-163 Singleton

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl



Width: 7-5/8 in Extends: 9 in Height: 8 in

H/CTR: 4-1/8 in (glass facing up)

Clear Glass Bowl Width: 7-5/8 in Height: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Back Plate covers a standard 4" recessed outlet box: 4.43" W., 8" ht., 0.87" depth		Fully dimmable with dimmable bulbs	