PROGRESS LIGHTING

Project:		
Fixture Type:		

Location:

Contact:



Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Width: 36 in Extends: 9 in Height: 8 in H/CTR: 5-5/8 in (glass facing up)

Clear Glass Bowl Width: 7-5/8 in Height: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Back Plate covers a standard 4" recessed outlet box: 8" W., 4.43" ht., 0.87" depth		Fully dimmable with dimmable bulbs	