

Project:
Fixture Type:
Location:
Contact:

Semblance LED

Wall Mounted • Damp Location Listed PROGRESS LED

Description:

Semblance Collection 24 in. Brushed Nickel Medium Modern 3CCT Integrated LED Linear Vanity Light

Specifications:

- · Diffused Plastic Diffuser
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.5 in W., 4.5 in ht., 1.26 in depth
- · Mounting backplate for outlet box included
- 10 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	22 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,627/74 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2016

P300406-009-CS



Dimensions:

Width: 24 in Extends: 3 in Height: 4-3/4 in



Semblance LED

Wall Mounted • Damp Location Listed PROGRESS LED

Photometrics:

P300406-009-CS

ELECTRICAL DATA P300406-009-CS

Input Voltage 120 V
Input Frequency 60 Hz
THD <20%

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature $-30 \, ^{\circ}\text{C}$ to $30 \, ^{\circ}\text{C}$

Dimming Yes*

Over-voltage, over-current, short-circuit protected *See Dimming Notes for more information



Semblance LED

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P300406-009-CS

P300406-009-CS is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton SAL06P
Leviton 6681
Leviton IPI06-1LZ
Leviton 6672
Leviton 6674
Lutron NTEVL-300
Lutron DVELV-300P
Lutron DVCL-253P
Lutron Caseta Wireless
Idevices IDEV009
Lutron AYCL-153P
Lutron ACL-153P
Lutron TGCL-153-PH-WH
Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.