PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P300413-015 Reiss

Reiss Collection One-Light Modern Farmhouse Polished Chrome Vanity Light

Category: Bath & Vanity Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Etched Glass Cylindrical



Width: 5 in Extends: 5-3/4 in Height: 7-7/8 in H/CTR: 3-7/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 4.37" W., 7.87" ht., 0.75" depth	Fully dimmable with dimmable bulbs		