

Project:			
Fixture Type:			
Location:			
Contact:			

## P300413-31M Reiss

Reiss Collection One-Light Modern Farmhouse Matte Black Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Width: 5 in Extends: 5-3/4 in Height: 7-7/8 in

H/CTR: 3-7/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

		9 - , .	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.37" W., 7.87" ht., 0.75" depth		Fully dimmable with dimmable bulbs	