## PROGRESS LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P300414-015 Reiss

Reiss Collection Two-Light Modern Farmhouse Polished Chrome Vanity Light

Category: Bath & Vanity Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Etched Glass Cylindrical

Width: 13-3/4 in Extends: 5-3/4 in Height: 7 in H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.37" ht., 0.75" depth		Fully dimmable with dimmable bulbs	