PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P300414-31M Reiss

Reiss Collection Two-Light Modern Farmhouse Matte Black Vanity Light

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Etched Glass Cylindrical



Width: 13-3/4 in Extends: 5-3/4 in Height: 7 in H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC Lamp Type A19		1-year Limited Warranty
Fixture can be installed with glass facing up or down	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.37" ht., 0.75" depth	Fully dimmable with dimmable bulbs		