

Project:		
Fixture Type:		
Location:		
Contact:		



P300415-015

Reiss

Reiss Collection Three-Light Modern Farmhouse Polished Chrome Vanity Light

Category: Bath & Vanity
Finish: Polished Chrome (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical

Width: 22-3/4 in Extends: 5-3/4 in Height: 7 in

H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

		0 , 1 ,		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed	
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty	
	Incandescent: 100-watt MAX per			
Fixture can be installed with glass		socket		
facing up or down		LED: 17.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.31" ht., 0.75" depth	Fully dimmable with dimmable bulbs			