

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |
| Contact: | | |



P300415-31M

Reiss

Reiss Collection Three-Light Modern Farmhouse Matte Black Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical

Width: 22-3/4 in Extends: 5-3/4 in Height: 7 in

H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------|------------------------------------|----------------------------|
| Wall mounted | 6 inches of wire supplied | (3) Medium Base (E26) Socket | cULus Damp Location Listed |
| Swivel mounting strap for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| | | Incandescent: 100-watt MAX per | |
| Fixture can be installed with glass | | socket | |
| facing up or down | | LED: 17.5-watt MAX per socket | |
| Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.31" ht., 0.75" depth | | Fully dimmable with dimmable bulbs | |