

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300416-009

Reiss

Reiss Collection Four-Light Modern Farmhouse Brushed Nickel Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical

Width: 31-5/8 in
 Extends: 5-3/4 in
 Height: 7 in
 H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical
 Width: 3-9/16 in
 Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.37" ht., 0.75" depth		Fully dimmable with dimmable bulbs	