## PROGRESS LIGHTING

| Project:      |  |  |
|---------------|--|--|
| Fixture Type: |  |  |
| Location:     |  |  |

Contact:

## P300416-015 Reiss

Reiss Collection Four-Light Modern Farmhouse Polished Chrome Vanity Light

Category: Bath & Vanity Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Etched Glass Cylindrical

Width: 31-5/8 in Extends: 5-3/4 in Height: 7 in H/CTR: 3-1/8 in (glass facing up)

Etched Glass Cylindrical Width: 3-9/16 in Height: 5-1/4 in

| MOUNTING  | ELECTRICAL                | LAMPING   | ADDITIONAL INFORMATION     |
|---|---------------------------|---|----------------------------|
| Wall mounted  | 6 inches of wire supplied | (4) Medium Base (E26) Socket  | cULus Damp Location Listed |
| Swivel mounting strap for outlet box included   | 120 VAC                   | Lamp Type A19   | 1-year Limited Warranty    |
| Fixture can be installed with glass<br>facing up or down                                |                           | Incandescent: 100-watt MAX per<br>socket<br>LED: 17.5-watt MAX per socket |                            |
| Canopy covers a standard 4"<br>recessed outlet box: 7.87" W.,<br>4.37" ht., 0.75" depth |                           | Fully dimmable with dimmable bulbs  |                            |