



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300423-31M Beckner

Beckner Collection Two-Light Matte Black Clear Glass Urban Industrial Bath Light with Vintage Brass Accents

**Category:** Bath & Vanity

**Finish:** Matte Black (Painted) with Vintage Brass accent

**Construction:** Steel Construction

**Glass/Shade:** Clear Bowl



Width: 14-5/8 in  
Extends: 6-3/8 in  
Height: 8-3/8 in  
H/CTR: 6-1/8 in (glass facing up)

Clear Bowl  
Width: 4-5/8 in  
Height: 3.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	