

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300425-009
Beckner

Beckner Collection Four-Light Brushed Nickel Clear Glass Urban Industrial Bath Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Bowl



Width: 33-3/4 in
Extends: 6-3/8 in
Height: 8-3/8 in
H/CTR: 6-1/8 in (glass facing up)

Clear Bowl
Width: 4-5/8 in
Height: 3.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	