

Project:			
Fixture Type:			
Location:			
Contact:			

P300426-163

Preston

Preston Collection One-Light Coastal Vintage Brass Bath and Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Bell



Width: 5-3/4 in Extends: 7-1/2 in Height: 9 in

H/CTR: 3-1/2 in (glass facing up)

Etched Opal Glass Bell Width: 5-3/4 in Height: 4-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.75" depth		Fully dimmable with dimmable bulbs	