

Project:		
Fixture Type:		
Location:		
Contact:		



P300428-163

Preston

Presto Collection Three-Light Coastal Vintage Brass Bath and Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Bell

Width: 22-1/8 in Extends: 7-3/8 in Height: 9 in

H/CTR: 4-1/2 in (glass facing up)

Etched Opal Glass Bell Width: 5-3/4 in Height: 4-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	