PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P300430-191 Copeland

Copeland Collection One-Light Brushed Gold Mid-Century Modern Vanity Light

Category: Bath & Vanity Finish: Brushed Gold (Plated) Construction: Steel Construction Glass/Shade: Etched Opal Glass Cone



Width: 6 in Extends: 7 in Height: 8 in H/CTR: 4-1/4 in (glass facing up)

Etched Opal Glass Cone Width: 6 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 7" ht., 0.75" depth		Fully dimmable with dimmable bulbs	