PROGRESS LIGHTING[™]

Project:

Fixture Type:

Location:

Contact:



P300432-191 Copeland

Copeland Collection Three-Light Brushed Gold Vanity Mid-Century Modern Vanity Light

Category: Bath & Vanity Finish: Brushed Gold (Plated) Construction: Steel Construction Glass/Shade: Etched Opal Glass Cone

Width: 24 in Extends: 7 in Height: 7-1/2 in H/CTR: 5-1/4 in (glass facing up)

Etched Opal Glass Cone Width: 6 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 75-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 15-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 7" W., 4.5" ht., 0.75" depth		bulbs	