

Project:		
Fixture Type:		
Location:		
Contact:		



P300433-191

Copeland

Copeland Collection Four-Light Brushed Gold Mid-Century Modern Vanity Light

Category: Bath & Vanity
Finish: Brushed Gold (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Cone

Width: 33 in Extends: 7 in Height: 7-1/2 in

H/CTR: 5-1/4 in (glass facing up)

Etched Opal Glass Cone

Width: 6 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth	Fully dimmable with dimmable bulbs		