

Project:		
Fixture Type:		
Location:		
Contact:		

## P300435-009

## **Northlake**

Northlake Collection Two-Light Brushed Nickel Clear Glass Transitional Bath Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl,



Width: 15.5 in Extends: 7.5 in Height: 8 in

H/CTR: 3 in (glass facing up)

Clear Glass Bowl Width: 4.5 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth	Fully dimmable with dimmable bulbs		