## PROGRESS LIGHTING

Project: Fixture Type: Location:

Contact:



Northlake Collection Two-Light Vintage Brass Clear Glass Transitional Bath Light

Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl,



Width: 15.5 in Extends: 7.5 in Height: 8 in H/CTR: 3 in (glass facing up)

Clear Glass Bowl Width: 4.5 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19 Incandescent: 60-watt MAX per	1-year Limited Warranty
Fixture can be installed with glass facing up or down		socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	