

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300436-163 Northlake

Northlake Collection Three-Light Vintage Brass Clear Glass Transitional Bath Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl,



Width: 24 in
Extends: 7.5 in
Height: 8 in
H/CTR: 3 in (glass facing up)

Clear Glass Bowl
Width: 4.5 in
Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	