

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300437-163 Northlake

Northlake Collection Four-Light Vintage Brass Clear Glass Transitional Bath Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl,

Width: 32.5 in
 Extends: 7.5 in
 Height: 8 in
 H/CTR: 3 in (glass facing up)

Clear Glass Bowl
 Width: 4.5 in
 Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	