

Project:			
Fixture Type:			
Location:			



P300437-31M

Northlake

Contact:

Northlake Collection Four-Light Matte Black Clear Glass Transitional Bath Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl,

Width: 32.5 in Extends: 7.5 in Height: 8 in

H/CTR: 3 in (glass facing up)

Clear Glass Bowl Width: 4.5 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	