

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_


Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300441-163 Fessler

Fessler Collection Four-Light Vintage Brass Opal Glass Farmhouse Bath Light

**Category:** Bath & Vanity  
**Finish:** Vintage Brass (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Opal Glass Bell,



Width: 29-1/8 in  
Extends: 7-1/8 in  
Height: 9-1/8 in  
H/CTR: 3-3/8 in (glass facing up)

Opal Glass Bell  
Width: 5 in  
Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	