



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300442-163 Haven

Haven Collection One-Light Vintage Brass Opal Glass Luxe Industrial Bath Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Opal Glass Bell



Width: 4-3/4 in
 Extends: 6-3/4 in
 Height: 7-7/8 in
 H/CTR: 4 in (glass facing up)

Opal Glass Bell
 Width: 4-3/4 in
 Height: 5.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.87" ht., 0.87" depth		Fully dimmable with dimmable bulbs	