



Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P300442-31M Haven

Haven Collection One-Light Matte Black Opal Glass Luxe Industrial Bath Light

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Opal Glass Bell



Width: 4-3/4 in  
 Extends: 6-3/4 in  
 Height: 7-7/8 in  
 H/CTR: 4 in (glass facing up)

Opal Glass Bell  
 Width: 4-3/4 in  
 Height: 5.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.87" ht., 0.87" depth		Fully dimmable with dimmable bulbs	