



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P300443-31M Haven

Haven Collection Two-Light Matte Black Opal Glass Luxe Industrial Bath Light

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Opal Glass Bell

Width: 16 in  
Extends: 6-3/4 in  
Height: 7 in  
H/CTR: 4-5/8 in (glass facing up)

Opal Glass Bell  
Width: 4-3/4 in  
Height: 5.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.75" ht., 0.87" depth		Fully dimmable with dimmable bulbs	