

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P300444-163
Haven

Haven Collection Three-Light Vintage Brass Opal Glass Luxe Industrial Bath Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Opal Glass Bell

Width: 24 in
 Extends: 6-3/4 in
 Height: 7 in
 H/CTR: 4-5/8 in (glass facing up)

Opal Glass Bell
 Width: 4-3/4 in
 Height: 5.5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.87" W., 4.75" ht., 0.87" depth		Fully dimmable with dimmable bulbs	