

Phase 5 LED

Wall Mounted • Damp Location Listed **PROGRESS LED**

Description:

Phase 5 Collection 32 in. Brushed Nickel Slim Modern 3CCT Integrated LED Linear Vanity Light


Specifications:

- White Polycarbonate Lens
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	22 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,512/72 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2022

P300450-009-CS



Dimensions:

Width: 32 in
Extends: 3-11/16 in
Height: 4-3/4 in (lens facing down)

P300450-009-CS

Dimming Notes:

P300450-009-CS is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTELV-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron Caséta

Lutron AYCL-153P

Lutron TGCL-153PH

Lutron TGCL-153PH

Lutron MAELV-600

Lutron AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

Photometrics:

ELECTRICAL DATA	P300450-009-CS
Input Voltage	120 VAC
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30
Dimming	Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information