

Project:			
Fixture Type:			
Location:			
Contact:			

Curvity LED

Wall Mounted • Damp Location Listed PROGRESS LED

Description:

Curvity LED Collection 24 in. Black Modern 3CCT Integrated LED Linear Vanity Light

Specifications:

- · White Polystyrene Lens
- Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- · Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	29 W	
Input Voltage	120 VAC	
Input Frequency	60 Hz	
Lumens/LPW (Delivered)	2,037/74 (LM-79)	
CRI	90 CRI	
Life (hours)	50000 (L70/TM-21)	
EMI/RFI	FCC Title 47, Part 15, Class B	
Warranty	5-year Limited Warranty	
Labels	cCSAus Damp Location Listed	
	Meets California Title 24 JA8-2022	

P300451-31M-CS





Dimensions:

Width: 24 in Extends: 3-15/16 in

Height: 4-1/2 in (lens facing up/down)



Curvity LED

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P300451-31M-CS

P300451-31M-CS is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron NTELV-300

Lutron DVELV-300P

Leviton 6681

Leviton 6672

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

Photometrics:

ELECTRICAL DATA P300451-31M-CS
Input Voltage 120 VAC

Input Frequency 60 Hz
THD <20%

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature $-30 \,^{\circ}\text{C}$ to 30 Dimming Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information