

Project:

Fixture Type:

Location:

Contact:

Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

PROGRESS

P300454-030-30

Description:


Captarent Collection 24 in. Round Illuminated Integrated LED White Modern Mirror

Specifications:

- Reflective Silver Glass Flat Round
- Diffused Glass Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- + 59 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	24 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,164/90 (LM-79)CRI 90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016



Dimensions:

Width: 24 in Extends: 1-5/8 in Height: 24 in

Reflective Silver Glass Flat Round Width: 0-1/4 in Height: 24 in



Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

Photometrics:

ELECTRICAL DATA	P300454-030-30	
Input Voltage	120 V	
Input Frequency	60 Hz	
THD	<20%	
EMI/RFI	FCC Title 47, Part 15, Class B	
Operating Temperature	-30 °C to 30 °C	
Dimming	Yes*	
Over-voltage, over-current, short-circuit protected		
*See Dimming Notes for more information		

P300454-030-30



Captarent LED

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P300454-030-30 is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton SAL06P
Leviton 6681
Leviton 6672
Leviton 6674
Lutron DVELV-300P
Lutron DVCL-253P
Lutron AYCL-153P
Lutron SCL-153P
Lutron TGCL-153-PH-WH
Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.