

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_



**P300460-009**  
**Vertex**

Vertex Collection Four-Light Brushed Nickel Clear Glass Contemporary Bath Light

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cone

Width: 29 in  
 Extends: 6-1/4 in  
 Height: 7.5 in  
 H/CTR: 5-1/8 in (glass facing up)

Clear Glass Cone  
 Width: 4-3/4 in  
 Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.06" W., 4.75" ht., 0.87" depth		Fully dimmable with dimmable bulbs	