



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300466-012 Adley

Adley Collection Two-Light Satin Brass Etched Opal Glass New Traditional Bath Vanity Light

Category: Bath & Vanity
Finish: Satin Brass (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Bell



Width: 13-7/8 in
Extends: 6 in
Height: 7-5/8 in
H/CTR: 5-3/8 in (glass facing up)

Etched Opal Glass Bell
Width: 4 in
Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.75" W., 4.5" ht., 0.8125" depth		Fully dimmable with dimmable bulbs	