

Captarent LED

• Damp Location Listed **PROGRESS LED**

Description:


Captarent Collection 30in. x 36 in. Oval Illuminated Integrated LED White Color Selectable Modern Mirror

Specifications:

- Mirror Glass Oval
- Dimmable to 10% brightness
- Fixture covers a standard 4" recessed outlet box
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	49 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered) at 3000K setting	1430/29 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2022



P300469-030-CS



Dimensions:

Width: 30 in
 Extends: 1-5/8 in
 Height: 36 in

P300469-030-CS

Photometrics:

ELECTRICAL DATA	P300469-030-CS
Input Voltage	120 VAC
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	