

Project:			
Fixture Type:			
Location:			
Contact:			

Captarent LED

• Damp Location Listed PROGRESS LED

Description:

Captarent Collection 36 in. x 42 in. Rectangular Illuminated Integrated LED White Color Selectable Modern Mirror

Specifications:

- · Mirror Glass Rectangle
- · Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box
- · Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	66 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1600/24 (LM-79)
at 3000K setting	
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2022

P300470-030-CS



Dimensions:

Width: 36 in Extends: 2-3/16 in Height: 42 in



Captarent LED

· Damp Location Listed PROGRESS LED

Photometrics:

P300470-030-CS

ELECTRICAL DATAP300470-030-CSInput Voltage120 VACInput Frequency60 HzTHD<20%</td>

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature -30 °C to 30

Dimming Yes*

Over-voltage, over-current, short-circuit protected *See Dimming Notes for more information