

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300472-31M Martenne

Martenne Collection One-Light Matte Black Modern Farmhouse Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Housing
Glass/Shade: Clear Seeded Glass Cone



Width: 4-5/8 in
Extends: 7 in
Height: 8-1/2 in
H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone
Width: 4-5/8 in
Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.81" ht., 4.5" depth			