

Project:

Fixture Type:

Location:

Contact:

P300473-196

Martenne

Martenne Collection Two-Light Aged Bronze Modern Farmhouse Vanity Light

Category: Bath & Vanity

Finish: Aged Bronze (Hand Painted)
Construction: Steel Housing

Glass/Shade: Clear Seeded Glass Cone



Width: 14 in Extends: 7 in Height: 8-1/2 in

H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone

Width: 4-5/8 in Height: 5-1/16 in

		8 9 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 6.68" W., 4.5" ht., 0.81" depth		bulbs.	